




Dry box glove

Natural rubber


6/10 mm



SCOPE


Life sciences (pharmaceutical industry, hospitals), nuclear, industry.

Natural rubber (polyisoprene) glove box glove MOUNTED ON A SUPPORT RING. This glove can be mounted on the glove box provided that the latter is equipped with an enclosure ring to receive this glove. Excellent precision, good resistance to alcohols, reducing acids and diluted bases. Low cost.



CE 0333					
			XX11X		VIRUS

IN COMPLIANCE WITH 2016/425 EUROPEAN REGULATION (CATEGORY 3 P.P.E.)



GENERAL INFORMATION

Chemical composition	Polyisoprene
Material code	H
Colour	Blond
Packaging	Individually packed in two-toned black and transparent, heat-sealed and easy-opening pouch. Pack of 10 units.
Care instructions	Store in the original packaging between +5°C and +25°C. Expiry date of 1 year in the original packaging. Wash with soapy water, rinse with clear water and then air-dry at a low temperature (<40°C).
Treatment	Non-recyclable. Disposal as simple non-toxic waste if not contaminated by a hazardous substance.
Sterilisation	Not available in decontaminated or decontaminated-sterile version.
Powdering	Standard: lightly powdered gloves.
Disinfectants	Excellent resistance to the following disinfectants: 0.25% Surfanios.
Dimensional tolerances	Thickness: 6/10 mm (min 5/10, max palm 7.5/10). Length tolerance (+/- 20 mm).

PHYSICOCHEMICAL PROPERTIES TEMPERATURE RANGE: -40 TO +80°C

Alcohols	— — —
Acids, bases	— — —
Strong oxidants	— — —
Uv, ozone, free radicals, natural ageing	— — —
Ketone solvents	— — —
Chlorinated solvents	— — —
Aromatic solvents	— — —
Aliphatic oils and solvents	— — —
Peracetic acid sterilisation (3%)	— — —
H2O2 Sterilisation (35%)	— — —
H2O2 Sterilisation (50%)	— — —
25-50 kGray gamma radiation	— — —
Autoclave sterilisation (121°C)	— — —
Protection from ionising radiation	non

* — — — Not recommended — — — Can be used under certain conditions — — — Acceptable — — — Recommended

MECHANICAL PROPERTIES

100% Modulus ⁽¹⁾	Tensile strength ⁽¹⁾	Elongation at break ⁽¹⁾	Puncture (EN 388)
< 1.5 MPa	> 20 MPa	> 500%	> 20 N

(1) (Iso 37 type 2)



The instruction leaflet, the EU Declaration of Conformity and the list of references are available on the website.

PIERCAN
17-23 rue Marcel Dassault CS 10028 - 93 141 BONDY CEDEX, France
T : +33 (0)1 45 88 66 27 - F : +33 (0)1 45 80 98 30
www.piercan.fr - piercan@piercan.fr

